



DESCRIPTION

Matt paint based on modified glycerophthalic resins.

FIELD OF USE

It is a paint ensuring the protection and beautification of ceilings, walls, doors, etc ...

TECHNICAL CHARACTERISTICS

- Aspect : Matt.
- Colors : Supplied in white and can be tinted with Colopâte.
- Spreading-rate : 6 à 7 m²/Kg depending on the porosity of the support.
- Dry extract : 84 % in weight +/- 2%.
- Density : 1.78 +/- 0.05 at 25°C.
- Viscosity : 135 KU +/- 6 at 25°C with the Krebs viscometer.

SURFACE PREPARATION

The work must be done in accordance with standard NF DTU59.1 and will be carried out with the greatest care.

APPLICATION PROPERTIES

COLOMAT can be applied by roller, brush or gun.
Application limit: Do not apply on condensing or frozen substrates, at temperatures below 5 ° C, or at relative humidity above 65%.

APPLICATION DETAILS OF USAGE

Dilution: D66 (White Spirit).

DRYING TIME

- Drying at 20 ° C and 60% humidity:
- Dust free : 30 minutes.
 - Dry: 1 hour.
 - Interval between coats: 12 hours.

RECOMMENDED SYSTEM

- INTERIOR (Hydraulic supports: contact us)

SYSTEM	NUMBER OF COATS
FORMORAL or COLOFIX	1
COLENDUIT EXTRA B505 or SP88	2
COLOSTOP	1
COLOMAT	2

STORAGE

The product can be stored for up to 2 years under good storage conditions away from sunlight and frost in its original closed packaging. However, it is recommended to shake the product before use.

PACKAGING

1 kg, 5 kg ,20 kg and 30 kg.

HEALTH & SAFETY

Health and safety information and precautions for use are detailed in the safety data sheet N° 38.

Edition : March 2021 by Colorado 03/21 (DC28 D).

N.B : The purpose of this technical data sheet is to provide information on the properties of our product. The information contained therein is based on our current knowledge of tests carried out with a constant concern for objectivity according to the conditions of use in accordance with standards or DTU in force; However, the information cannot replace an appropriate description and the state of the funds to be painted. This descriptive technical sheet cancels and replaces any sheet relating to the same product. The above technical data does not imply acceptance of the guarantees. Close the pot tightly after use. Help preserve the environment by not disposing of waste in the drains or household waste. Please return your empty jar to a recycling center. For your unused product, please contact your local authorities for information on disposal and collection.

COLORADO is certified ISO 9001, ISO 14001 and ISO 45001